

Varistar CP Steel Door, Perforated With Multi-Point Locking



EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

FEATURES

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFICATIONS

Product Type: Cabinet Door

Material: Steel

Table 1/1

Catalog Number	Rack Height	Package Quantity	Finish	Locking Type	Type	Quick Ship
21630-533	24U	1	Powder Coated	3-Point Locking	Steel Door, Perforated	No
21630-534	24U	1	Powder Coated	3-Point Locking	Steel Door, Perforated	No
21630-535	29U	1	Powder Coated	3-Point Locking	Steel Door, Perforated	No
21630-536	29U	1	Powder Coated	3-Point Locking	Steel Door, Perforated	No

CatalogNumber	Rack Height	Package Quantity	Finish	Locking Type	Type	Quick Ship
21630-537	33U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-538	33U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-539	38U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-540	38U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-541	42U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-542	42U	1	Powder Coated	4-Point Locking	Steel Door, Perforated	No
21630-543	47U	1	Powder Coated	5-Point Locking	Steel Door, Perforated	No
21630-544	47U	1	Powder Coated	5-Point Locking	Steel Door, Perforated	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE