

# Varistar CP Steel Door, Plain With 3-Point Locking, IP55



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

## FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

## SPECIFICATIONS

**Locking Type:** 3-Point Locking

**Product Type:** Cabinet Door

**Protection Rating:** IP55

**Material:** Steel

Table 1/2

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-210	24U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-216	24U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-211	29U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-217	29U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Complies With	Finish
21630-212	33U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-218	33U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-213	38U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-219	38U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-214	42U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-220	42U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-215	47U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated
21630-171	47U	1	Black Grey	RAL 7021	IEC 61587-1	Powder Coated

Table 2/2			
Catalog Number	Type	Works With	Quick Ship
21630-210	Steel Door	Varistar CP	No
21630-216	Steel Door	Varistar CP	No
21630-211	Steel Door	Varistar CP	No
21630-217	Steel Door	Varistar CP	No
21630-212	Steel Door	Varistar CP	No
21630-218	Steel Door	Varistar CP	No
21630-213	Steel Door	Varistar CP	No
21630-219	Steel Door	Varistar CP	No
21630-214	Steel Door	Varistar CP	No

Catalog Number	Type	Works With	Quick Ship
21630-220	Steel Door	Varistar CP	No
21630-215	Steel Door	Varistar CP	No
21630-171	Steel Door	Varistar CP	No

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**