

Varistar CP Steel Door, Plain With 3-Point Locking, Shortened



Shortened door available for IP20, IP55 applications.

FEATURES

Height of connection plate 400 mm

SPECIFICATIONS

Locking Type: 3-Point Locking
Product Type: Cabinet Door
Protection Rating: IP20
Material: Steel

Table 1/1

Catalog Number	Rack Height	Package Quantity	Color	Color Code	Finish	Quick Ship
21630-336	38U	1	Black Grey	RAL 7021	Powder Coated	No
21630-338	42U	1	Black Grey	RAL 7021	Powder Coated	No
21630-340	47U	1	Black Grey	RAL 7021	Powder Coated	No
21630-337	38U	1	Black Grey	RAL 7021	Powder Coated	No
21630-339	42U	1	Black Grey	RAL 7021	Powder Coated	No

CatalogNumber	Rack Height	Package Quantity	Color	Color Code	Finish	Quick Ship
21630-341	47U	1	Black Grey	RAL 7021	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE