

# VMEbus J2 Backplane



The nVent SCHROFF VMEbus Backplanes have outstanding high-frequency noise suppression and very high MTBF values due to ceramic capacitors and SMD fabrication technology.

#### **CERTIFICATIONS**





#### **FEATURES**

In accordance with ANSI/VITA 1-1994 VME64 standard

3 U with J2 plane

Connection or isolation between the digital GND and chassis GND can be changed via screw

Termination passive

Supply voltages can be provided via powerbugs (ring tag M4) or FASTONs

Multiple backplanes can be placed side by side without loss of slot space

#### **SPECIFICATIONS**

Table 1/2						
Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23001-032	Backplane	2	3U	VMEbus, J2	Slot 1 Left	4HP
23001-033	Backplane	3	3U	VMEbus, J2	Slot 1 Left	4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23001-034	Backplane	4	3U	VMEbus, J2	Slot 1 Left	4HP
23001-035	Backplane	5	3U	VMEbus, J2	Slot 1 Left	4HP
23001-036	Backplane	6	3U	VMEbus, J2	Slot 1 Left	4HP
23001-040	Backplane	10	3U	VMEbus, J2	Slot 1 Left	4HP
23001-046	Backplane	16	3U	VMEbus, J2	Slot 1 Left	4HP
23001-051	Backplane	21	3U	VMEbus, J2	Slot 1 Left	4HP

Table 2/2							
Catalog Number	Connector Type	Power Connector Type	Package Quantity	Quick Ship			
23001-032	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-033	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-034	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-035	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-036	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-040	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-046	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			
23001-051	DIN 41612, C96	Power Bugs for M4 Cable Lugs	1	No			

# ADDITIONAL PRODUCT DETAILS

Other configurations available on request.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

# Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF** TRACHTE