

H-MSM Conduit/Pipe to Flange Clip, Side Mount



CERTIFICATIONS



FEATURES

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

SPECIFICATIONS

Finish: nVent CADDY Armour


Material: Spring Steel

Table 1/1

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
16M24SM	173720	23.4 - 35 mm	3 - 8 mm	120N	UL, cUL
20M24SM	171720	35 - 42 mm	3 - 8 mm	120N	cUL, UL
24M24SM	176690	42 - 50 mm	3 - 8 mm	120N	cUL, UL

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
32M24SM	173830	50 - 60 mm	3 - 8 mm	120N	UL, cUL
812M24SM	160050	18 - 30 mm	3 - 8 mm	120N	UL, ITB, cUL
16M58SM	173730	23.4 - 35 mm	8 - 14 mm	120N	UL, cUL
20M58SM	173770	35 - 42 mm	8 - 14 mm	120N	
24M58SM	173800	42 - 50 mm	8 - 14 mm	120N	cUL, UL
32M58SM	173840	50 - 60 mm	8 - 14 mm	120N	UL, cUL
812M58SM	160060	18 - 30 mm	8 - 14 mm	120N	UL, cUL, ITB
812M912SM	160070	18 - 30 mm	14 - 20 mm	120N	ITB, UL, cUL
16M912SM	173740	23.4 - 35 mm	14 - 20 mm	120N	cUL, UL
20M912SM	173780	35 - 42 mm	14 - 20 mm	120N	
24M912SM	173810	42 - 50 mm	14 - 20 mm	120N	cUL, UL
32M912SM	173850	50 - 60 mm	14 - 20 mm	120N	cUL, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

