


Novastar Raised Top Cover

Power Utilities



Raised top cover for better ventilation and heat escape.
Novastar raised top cover is robust and not dismountable from the outside.

CERTIFICATIONS



FEATURES

Raised Top cover (31 mm) with all-round air gap of 10 mm

Top cover attached from the inside (no screws on the outside)

Suitable for placing heavy parts on the top cover

Incl. grounding

SPECIFICATIONS

Table 1/1						
Catalog Number	Depth	Color	Color Code	Product Type	Type	Width
25230-010	500 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-046	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-045	900 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-012	800 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm
25230-011	600 mm	Black Grey	RAL 7021	Cabinet/Rack Top Cover	Raised	553 mm

ADDITIONAL PRODUCT DETAILS

Please order lifting eye separately if required.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE