

# Varistar Server Cabinet, RAL 9003, Side-by-Side



Server rack for high static load requirements, completely assembled and grounded including side by side kits powder coated in white.

## CERTIFICATIONS



## FEATURES

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different servers possible

Server cabinet with perforated doors, airflow rate 78 %

RAL 9003 (white)

## SPECIFICATIONS

Table 1/3

| Catalog Number | Type         | Frame Material | Cladding Material | Frame Color  | Frame Color Code | Cladding Color |
|----------------|--------------|----------------|-------------------|--------------|------------------|----------------|
| 12130-275      | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-276      | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-285      | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |

| CatalogNumber | Type         | Frame Material | Cladding Material | Frame Color  | Frame Color Code | Cladding Color |
|---------------|--------------|----------------|-------------------|--------------|------------------|----------------|
| 12130-286     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-279     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-280     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-289     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-290     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-283     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-284     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-293     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |
| 12130-294     | Side-by-Side | Steel          | Steel             | Signal White | RAL 9003         | Signal White   |

Table 2/3

| Catalog Number | Cladding Color Code | Rack Height | Height | Width | Depth  | Static Load |
|----------------|---------------------|-------------|--------|-------|--------|-------------|
| 12130-275      | RAL 9003            | 42U         | 2000mm | 600mm | 1000mm | 1600kg      |
| 12130-276      | RAL 9003            | 42U         | 2000mm | 800mm | 1000mm | 1600kg      |
| 12130-285      | RAL 9003            | 42U         | 2000mm | 600mm | 1200mm | 1600kg      |
| 12130-286      | RAL 9003            | 42U         | 2000mm | 800mm | 1200mm | 1600kg      |
| 12130-279      | RAL 9003            | 47U         | 2200mm | 600mm | 1000mm | 1600kg      |
| 12130-280      | RAL 9003            | 47U         | 2200mm | 800mm | 1000mm | 1600kg      |
| 12130-289      | RAL 9003            | 47U         | 2200mm | 600mm | 1200mm | 1600kg      |

| CatalogNumber | Cladding Color Code | Rack Height | Height | Width | Depth  | Static Load |
|---------------|---------------------|-------------|--------|-------|--------|-------------|
| 12130-290     | RAL 9003            | 47U         | 2200mm | 800mm | 1200mm | 1600kg      |
| 12130-283     | RAL 9003            | 52U         | 2450mm | 600mm | 1000mm | 1600kg      |
| 12130-284     | RAL 9003            | 52U         | 2450mm | 800mm | 1000mm | 1600kg      |
| 12130-293     | RAL 9003            | 52U         | 2450mm | 600mm | 1200mm | 1600kg      |
| 12130-294     | RAL 9003            | 52U         | 2450mm | 800mm | 1200mm | 1600kg      |

Table 3/3

| Catalog Number | Quick Ship |
|----------------|------------|
| 12130-275      | No         |
| 12130-276      | No         |
| 12130-285      | No         |
| 12130-286      | No         |
| 12130-279      | No         |
| 12130-280      | No         |
| 12130-289      | No         |
| 12130-290      | No         |
| 12130-283      | No         |
| 12130-284      | No         |
| 12130-293      | No         |
| 12130-294      | No         |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**