

# nVent CADDY Speed Link SLK with Threaded Stud End



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

## SPECIFICATIONS

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Static Load Safety Factor:</b> | 5:1                            |
| <b>Finish:</b>                    | Electrogalvanized              |
| <b>Material:</b>                  | Steel;Polypropylene;Zinc Alloy |
| <b>Complies With:</b>             | SMACNA HVAC-DCS                |


Table 1/2

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Rod Size (RS) | Screw Length (L) | Height (H) |
|----------------|----------------|--------------------|------------------|---------------|------------------|------------|
| SLK2L5SEM8     | 196563         | 2 mm               | 5m               | 8             | 45mm             | 55 mm      |

| CatalogNumber | Article Number | Wire Rope Diameter | Wire Rope Length | Rod Size (RS) | Screw Length (L) | Height (H) |
|---------------|----------------|--------------------|------------------|---------------|------------------|------------|
| SLK2L3SEM8    | 196561         | 2 mm               | 3m               | 8             | 45mm             | 55 mm      |
| SLK3L5SEM10   | 196720         | 3 mm               | 5m               | 10            | 45mm             | 62 mm      |
| SLK3L2SEM10   | 196718         | 3 mm               | 2m               | 10            | 45mm             | 62 mm      |
| SLK3L3SEM10   | 196719         | 3 mm               | 3m               | 10            | 45mm             | 62 mm      |

| Table 2/2      |                |           |               |           |             |                |
|----------------|----------------|-----------|---------------|-----------|-------------|----------------|
| Catalog Number | Article Number | Width (W) | Thickness (T) | Angle (a) | Static Load | Certifications |
| SLK2L5SEM8     | 196563         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        | UL, cUL        |
| SLK2L3SEM8     | 196561         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        | cUL, UL        |
| SLK3L5SEM10    | 196720         | 24 mm     | 16 mm         | 90 ° Max  | 890N        |                |
| SLK3L2SEM10    | 196718         | 24 mm     | 16 mm         | 90 ° Max  | 890N        |                |
| SLK3L3SEM10    | 196719         | 24 mm     | 16 mm         | 90 ° Max  | 890N        |                |

## DIAGRAMS



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**

