

ProLine G2 Vented Plinth Base Cover



The Vented Plinth Base Covers replace the traditional solid plinth base covers that mount width-wise across the front and rear of the enclosure. Vented covers allow air to enter the enclosure from below, and are used in conjunction with the Vented Gland Plate.

FEATURES

Mounting hardware included

SPECIFICATIONS

- Thickness:** 1.52mm
- Color:** Jet Black
- Finish:** Powder Coated
- Color Code:** RAL 9005

Table 1/1					
Catalog Number	Article Number	Frame Type	Fits Frame Width	Material	Quick Ship
P2APBVC8	36148	Single-Bay	800mm	Mild Steel	No
P2APBVC18	36154	Double-Bay	1800mm	Mild Steel	No
P2APBVC16	36153	Double-Bay	1600mm	Mild Steel	No
P2APBVC6	36147	Single-Bay	600mm	Mild Steel	No
P2APBVC12	36152	Double-Bay	1200mm	Mild Steel	No
P2APBVC10	36151	Single-Bay	1000mm	Mild Steel	No

ADDITIONAL PRODUCT DETAILS

Please note that a standard 100mm Solid Plinth Base must be ordered separately, as Vented Plinth Base Covers are replacements for the front and rear covers only. Vented Gland Plate also sold separately, but required for successful air passage.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE