

Socket Strip, SCHUKO, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPECIFICATIONS

Length:	438.5mm
Material:	Aluminum; Polyamide
Product Type:	Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-345	SCHUKO	8	No	230V		1

CatalogNumber	Socket Type	SocketQuantity	Switched Outlets	Voltage AC	Function	Package Quantity
60110-344	SCHUKO	8	No	230V		1
60110-343	SCHUKO	8	No	230V		1
60110-352	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-354	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-353	SCHUKO	6	No	230V	Overcurrent Protection	1

Table 2/2

Catalog Number	Color	Depth	Finish	Quick Ship
60110-345	Red	44mm	Anodized	No
60110-344	Black	44mm	Anodized	No
60110-343	Grey	44mm	Anodized	No
60110-352	Grey	44mm	Anodized	No
60110-354	Red	44mm	Anodized	No
60110-353	Black	44mm	Anodized	No

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE