

# Cable Spool



## CERTIFICATIONS



## FEATURES

Cut to length as needed

Pre-stretched restraint cable

Certified chemically compatible with CPVC piping systems

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

## SPECIFICATIONS

**Finish:** Pregalvanized;Painted

**Material:** Steel

Table 1/1

| Catalog Number | Article Number | Brace Size | Diameter | Cable Length | UL Listed Load | Color |
|----------------|----------------|------------|----------|--------------|----------------|-------|
| CSB12CBL       | 402190         | #12        | 2.4 mm   | 76.2m        | 1859N          | Red   |

| CatalogNumber | Article Number | Brace Size | Diameter | Cable Length | UL Listed Load | Color |
|---------------|----------------|------------|----------|--------------|----------------|-------|
| CSB18CBL      | 402191         | #18        | 3.2 mm   | 76.2m        | 3434N          | White |
| CSB36CBL      | 402192         | #36        | 4.8 mm   | 76.2m        | 8490N          | Blue  |

## ADDITIONAL PRODUCT DETAILS

Cable is powder coated.

FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® piping systems and products made with TempRite® Technology." "The FBC System Compatible Logo, FBC™, FlowGuard Gold®, BlazeMaster®, Corzan®, and TempRite® are trademarks of Lubrizol Advanced Materials, Inc. or its affiliates.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

