

# Hazardous Location Door Switch, 0.39x0.71x1.10, Gray, Plastic

## CATALOG NUMBER

## LEDHLSWITCH



The Hazardous Location Door Switch is designed to be used with nVent HOFFMAN Hazardous Location LED Lights in Class 1, Division 2 hazardous areas. The included hardware kit allows the door switch to easily be mounted and maintain the enclosure rating up to UL Type 4X. This versatile switch activates the LED light when the enclosure door is opened and can be mounted on any flange of the enclosure. The included five-foot connect cable allows ease of wiring to the enclosure back panel.

## INDUSTRY STANDARDS

Switch Rating

Explosion-proof for Class 1, Division 2, Groups A, B, C, and D

## FEATURES

Class 1, Division 2 hazardous areas

Maintains the enclosure rating up to UL Type 4X

Five foot connection cable

Ease of wiring to the enclosure back panel

## PRODUCT ATTRIBUTES

Article Number: 27194

Height: 10mm

Width: 18mm

Depth: 28mm

Material: Plastic

Finish: Smooth

Color: Gray

Operating Temperature: -20 to 90°C

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**