

# Window Door, ADT



Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

## FEATURES

Description: To replace the standard door, it provides a clear view of the components installed inside the enclosure. The lock(s) are interchangeable with all nVent HOFFMAN's standard lock(s).

Material: 1.2 mm mild steel / 1.5 mm for enclosures with a height or width of 500 mm or greater / 2 mm for enclosures with a height or width of 800 mm or greater and 3 mm transparent acrylic glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP55, IK 07.

Pack quantity: 1 door.

## SPECIFICATIONS

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Thickness | Latch Quantity |
|----------------|----------------|--------|-------|-------|-----------|----------------|
| ADT03025R5     | ADT03025R5     | 295mm  | 245mm | 15mm  | 1.2mm     | 1              |
| ADT03030R5     | ADT03030R5     | 295mm  | 294mm | 15mm  | 1.2mm     | 1              |
| ADT04030R5     | ADT04030R5     | 395mm  | 294mm | 15mm  | 1.2mm     | 1              |
| ADT04040R5     | ADT04040R5     | 395mm  | 394mm | 15mm  | 1.2mm     | 1              |
| ADT05030R5     | ADT05030R5     | 495mm  | 294mm | 15mm  | 1.5mm     | 1              |
| ADT05040R5     | ADT05040R5     | 495mm  | 394mm | 15mm  | 1.5mm     | 1              |
| ADT06040R5     | ADT06040R5     | 595mm  | 394mm | 15mm  | 1.5mm     | 2              |
| ADT06050R5     | ADT06050R5     | 595mm  | 495mm | 15mm  | 1.5mm     | 2              |
| ADT06060R5     | ADT06060R5     | 595mm  | 595mm | 15mm  | 1.5mm     | 2              |
| ADT07050R5     | ADT07050R5     | 695mm  | 495mm | 15mm  | 1.5mm     | 2              |
| ADT08060R5     | ADT08060R5     | 795mm  | 595mm | 15mm  | 2mm       | 2              |
| ADT10060R5     | ADT10060R5     | 995mm  | 595mm | 15mm  | 2mm       | 1              |
| ADT10080R5     | ADT10080R5     | 995mm  | 795mm | 15mm  | 2mm       | 1              |
| ADT12060R5     | ADT12060R5     | 1195mm | 595mm | 15mm  | 2mm       | 1              |
| ADT12080R5     | ADT12080R5     | 1195mm | 795mm | 15mm  | 2mm       | 1              |

## ADDITIONAL PRODUCT DETAILS

---

\* 3 point espagnolette locking. Not suitable for AFS.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**