nVent LENTON

We connect and protect

A2D6 Mechanical Anchor for Future Extension, Plain, 16 mm, #5, 15M

CATALOG NUMBER

EL16A2D6



FEATURES

- Replaces conventional hooked reinforcing bar
- Commonly used for future extensions in both beam/column and roof/column connections
- Head area exceeds 5x bar area (net 4x)

PRODUCT ATTRIBUTES

- Material: Steel
- Finish: Plain
- 100% U.S. Domestic Content: Yes
- Rebar Size, Metric: 16 mm
- Rebar Size, US: #5
- Rebar Size, Canada: 15M
- Diameter 1 (Ø1): 38 mm
- Length 1 (L1): 56 mm
- Bar Depth (BD): 22mm
- Unit Weight: 0.43 kg
- Designed to Meet: AASHTO;ABNT NBR 8548:1984;ACI 318 Type 1 (125% Specified Yield);ACI 318 Type 2 (Specified Tensile);ACI 349;ACI 359;AS3600

ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.