nVent SCHROFF

We connect and protect

Fuse Holder, Long Type

CATALOG NUMBER

69004-098



For glass fuse inserts 5 x 20 mm to DIN 41 571, 250 VAC, 6.3 A.

CERTIFICATIONS

RoHS COMPLIANT

EAC

FEATURES

- For glass fuse inserts 5 x 20 mm to DIN 41 571, 250 VAC, 6.3 A
- Long type for mounting plane 1
- Contacts silver plated

PRODUCT ATTRIBUTES

- Product Type: Fuse Holder
- Contact Material: Copper alloy
- Material: Polybutylene Terephthalate
- Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Required front panel drill hole: Ø 9 mm.

Dimensions of connecting pins: 0.7 × 0.6 mm.

Please take into consideration that deliveries may be carried out inthe stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.