

300M Universal Beam Clamp



CERTIFICATIONS



FEATURES

Universal beam clamp for standard beams

Structural attachment (with infinite adjustment) to top or bottom flange of metal beams to support hanger rod

Including set screw and lock nut

SPECIFICATIONS

Material: Cast Iron

Finish: Electrogalvanized

Table 1/2

Catalog Number	Article Number	Hole Type	Hole Size (HS)	Thread Size (TS)	Flange Thickness (FT)	A
30009MM	389500	Plain	9 mm		18 mm Max	21 mm
30011MM	389510	Plain	11 mm		20 mm Max	23 mm
30013MM	389520	Plain	13 mm		26 mm Max	35 mm

CatalogNumber	Article Number	Hole Type	Hole Size (HS)	Thread Size (TS)	Flange Thickness (FT)	A
30017MM	389505	Plain	17 mm		28 mm Max	30 mm
300M8	386810	Threaded		M8	18 mm Max	21 mm
300M6	386805	Threaded		M6	18 mm Max	21 mm
300M10	386820	Threaded		M10	20 mm Max	23 mm
300M12	386830	Threaded		M12	26 mm Max	35 mm


Table 2/2

Catalog Number	Article Number	Torque (TQ)	Static Load	Certifications
30009MM	389500	14 N·m Min	1200N	ITB, VdS G4005005
30011MM	389510	14 N·m Min	2500N	FM Approved, Pipe Hanger Components, ITB, VdS G4005005
30013MM	389520	14 N·m Min	3500N	VdS G4913044, ITB, FM Approved, Pipe Hanger Components
30017MM	389505	14 N·m Min	5500N	ITB, FM Approved, Pipe Hanger Components, VdS G4031026
300M8	386810	14 N·m Min	1200N	ITB, VdS G4005005
300M6	386805	14 N·m Min	1200N	
300M10	386820	14 N·m Min	2500N	VdS G4005005, FM Approved, Pipe Hanger Components, ITB
300M12	386830	14 N·m Min	3500N	ITB, FM Approved, Pipe Hanger Components, VdS G4913044

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

