

Enclosure Pole Fixation, EPF



This pole fixation kit allows the enclosure to be mounted on a variety of poles at the desired height.

FEATURES

Description: Accessory to fix enclosures onto poles. Maximum load of 900 N.

Material: Galvanized steel.

Minimum pole diameter: 80 mm.

Maximum pole diameter: 250 mm.

Pack quantity: 2 profiles, 2 circular mounting strips for pole attachment and mounting accessories.

SPECIFICATIONS

Thickness: 3mm
Finish: Galvanized
Material: Mild Steel

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Product Family |
|----------------|----------------|--------|-------|-------|--------------------------|---------------------------------|
| EPF0300 | EPF0300 | 35mm | 296mm | 25mm | Mild Steel, Polyester | Wall Mounted, Terminal Boxes |
| EPF0600 | EPF0600 | 35mm | 596mm | 25mm | Mild Steel, Polyester | Wall Mounted, Terminal Boxes |
| EPF0500 | EPF0500 | 35mm | 496mm | 25mm | Mild Steel, Polyester | Wall Mounted, Terminal Boxes |
| EPF0400 | EPF0400 | 35mm | 396mm | 25mm | Mild Steel, Polyester | Wall Mounted, Terminal Boxes |
| EPF0800 | EPF0800 | 35mm | 796mm | 25mm | Mild Steel, Polyester | Wall Mounted, Terminal Boxes |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE