

LSZH Coated Clip



nVent PYROTENAX LSZH Coated Clip is a range of low smoke zero halogen (LSZH) coated copper fixing clips for mineral insulated (MI) cables. Available in various sizes and colors. For fixing LSZH covered light or heavy duty MI cables.

FEATURES

Simple to install

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Table 1/1

Catalog Number	Tube/Cable Diameter	Color
RCHL26BK	6.6 mm	Black
RCHL26OR	6.6 mm	Orange
RCHL26RD	6.6 mm	Red
RCHL26WH	6.6 mm	White
RCHL28BK	7.3 mm	Black
RCHL28OR	7.3 mm	Orange
RCHL28RD	7.3 mm	Red
RCHL28WH	7.3 mm	White

Catalog Number	Tube/Cable Diameter	Color
RCHL30BK	7.7 mm	Black
RCHL30OR	7.7 mm	Orange
RCHL30RD	7.7 mm	Red
RCHL30WH	7.7 mm	White
RCHL32BK	8.1 mm	Black
RCHL32OR	8.1 mm	Orange
RCHL32RD	8.1 mm	Red
RCHL32WH	8.1 mm	White
RCHL34BK	8.7 mm	Black
RCHL34OR	8.7 mm	Orange
RCHL34RD	8.7 mm	Red
RCHL34WH	8.7 mm	White
RCHL37BK	9.4 mm	Black
RCHL37OR	9.4 mm	Orange
RCHL37RD	9.4 mm	Red
RCHL37WH	9.4 mm	White
RCHL40BK	10.3 mm	Black
RCHL40OR	10.3 mm	Orange

Catalog Number	Tube/Cable Diameter	Color
RCHL40RD	10.3 mm	Red
RCHL40WH	10.3 mm	White
RCHL43BK	10.9 mm	Black
RCHL43OR	10.9 mm	Orange
RCHL43RD	10.9 mm	Red
RCHL43WH	10.9 mm	White
RCHL47BK	12.4 mm	Black
RCHL47OR	12.4 mm	Orange
RCHL47RD	12.4 mm	Red
RCHL47WH	12.4 mm	White
RCHL51BK	13.1 mm	Black
RCHL51OR	13.1 mm	Orange
RCHL51RD	13.1 mm	Red
RCHL51WH	13.1 mm	White
RCHL54BK	13.6 mm	Black
RCHL54OR	13.6 mm	Orange
RCHL54RD	13.6 mm	Red
RCHL54WH	13.6 mm	White

Catalog Number	Tube/Cable Diameter	Color
RCHL59BK	15.2 mm	Black
RCHL59GY	15.2 mm	Grey
RCHL59OR	15.2 mm	Orange
RCHL59RD	15.2 mm	Red
RCHL59WH	15.2 mm	White
RCHL63BK	16.4 mm	Black
RCHL63OR	16.4 mm	Orange
RCHL63RD	16.4 mm	Red
RCHL63WH	16.4 mm	White
RCHL67BK	16.9 mm	Black
RCHL67OR	16.9 mm	Orange
RCHL67RD	16.9 mm	Red
RCHL67WH	16.9 mm	White
RCHL71BK	18.1 mm	Black
RCHL71OR	18.1 mm	Orange
RCHL71RD	18.1 mm	Red
RCHL71WH	18.1 mm	White
RCHL75BK	19.2 mm	Black

Catalog Number	Tube/Cable Diameter	Color
RCHL75OR	19.2 mm	Orange
RCHL75RD	19.2 mm	Red
RCHL75WH	19.2 mm	White
RCHL79BK	20 mm	Black
RCHL79OR	20 mm	Orange
RCHL79RD	20 mm	Red
RCHL79WH	20 mm	White
RCHL88BK	21.9 mm	Black
RCHL88OR	21.9 mm	Orange
RCHL88RD	21.9 mm	Red
RCHL88WH	21.9 mm	White
RCHL101BK	25.8 mm	Black
RCHL101OR	25.8 mm	Orange
RCHL101RD	25.8 mm	Red

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT