

Standard Termination Kit with Long Tails



nVent PYROTENAX Standard Termination Kit With Long Tails are a range of standard screw-on termination kits to install long earth tail seals (RPSL) on light or heavy duty mineral insulated (MI) cables. Available in various sizes, with a continuous operating temperature range from 80 °C to +105 °C. Suitable for the majority of general wiring applications.

FEATURES

- Simple to install
- Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Max Operating Temperature:	105 °C
Voltage Rating:	500 – 750 V

Catalog Number
RPSL1H1025
RPSL1H1625
RPSL1H2.520
RPSL1H2532
RPSL1H3532
RPSL1H5040
RPSL1H620

Catalog Number
RPSL2H1.520
RPSL2H1032
RPSL2H1640
RPSL2H2.520
RPSL2H2540
RPSL2H425
RPSL2H625
RPSL2L1.520
RPSL2L120
RPSL2L2.520
RPSL2L420
RPSL3H1.520
RPSL3H1032
RPSL3H1640
RPSL3H2.525
RPSL3H2540
RPSL3H425
RPSL3H625

Catalog Number
RPSL3L1.520
RPSL3L120
RPSL3L2.520
RPSL4H1.520
RPSL4H1032
RPSL4H1640
RPSL4H2.525
RPSL4H2540
RPSL4H425
RPSL4H632
RPSL4L1.520
RPSL4L120
RPSL4L2.520
RPSL7H1.525
RPSL7H2.525
RPSL7L1.525
RPSL7L125
RPSL7L2.525

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT