


# Metal Mesh

nVent RAYCHEM U-ACC-MM-XX is a galvanized metal mesh. Available in two sizes, 10 m (U-ACC-MM-10) and 25 m (U-ACC-MM-25).



## FEATURES

Simple and fast to install: easy roll out

## SPECIFICATIONS

**Grid:** 10 mm  
**Finish:** Galvanized  
**Material:** Metal

Table 1/1

| Catalog Number | Item Name   | Length | Width |
|----------------|-------------|--------|-------|
| 476660-000     | U-ACC-MM-10 | 10 m   | 1 m   |
| 726604-000     | U-ACC-MM-25 | 25 m   | 1 m   |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,  
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM   PYROTENAX   TRACER   NUHEAT**