

# EuropacPRO 19" Subrack Kit for Railway, Shielded, EN 50155, CompactPCI

## Servicios públicos de energía



Subrack for Railway applications, conform to EN50155 standard, for Compact PCI applications.

### CERTIFICACIONES



### CARACTERÍSTICAS

Shock and vibration tested to EN 50155, part 12.2.11

The 19" bracket is firmly fixed to the side panel (tox-cold welded) and is especially suited for high mechanical stresses (vibration resistance)

The double 19" screwing position adds to additionally safety (NFF standard)

IP 20, in accordance with IEC 60529

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Aluminum construction

Supplied as space-saving flat-pack

### ESPECIFICACIONES

Table 1/3

| Número de catálogo | Rack Height | Package Quantity | For Mounting | Board Depth | EMC Gasket Type | Shock and Vibration Tolerance |
|--------------------|-------------|------------------|--------------|-------------|-----------------|-------------------------------|
| 21500-081          | 3 U         | 1                | Backplane    | 160 mm      | Textile         | 5 g (force)                   |
| 21500-082          | 6 U         | 1                | Backplane    | 160 mm      | Textile         | 5 g (force)                   |

Table 2/3

| Número de catálogo | Handle Included | Montaje | Cumple con                                                         | Profundidad | EMC Shielding | Product Type    |
|--------------------|-----------------|---------|--------------------------------------------------------------------|-------------|---------------|-----------------|
| 21500-081          | Sí              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, EN 50155 part 12.2.11 | 235 mm      | Sí            | Subrack/Chassis |
| 21500-082          | Sí              | Rack    | IEC 60297-3-103, IEEE 1101.10, IEEE 1101.11, EN 50155 part 12.2.11 | 235 mm      | Sí            | Subrack/Chassis |

Table 3/3

| Número de catálogo | Rack Width | Carga estática |
|--------------------|------------|----------------|
| 21500-081          | 84 HP      | 15 kgf         |
| 21500-082          | 84 HP      | 15 kgf         |

## ADDITIONAL PRODUCT DETAILS

Test reports are available online.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**