

SC Series, Above Insulation Splice Kit, Direct (No cold lead)



nVent RAYCHEM JB-SPLICE SC-A is a splice box that integrates a support bracket and insulation entry kit by using a hollow stand to feed the heating cable into the junction box .

CARACTERÍSTICAS

Splice kit for all 2SC and 3SC heaters

Simplified Bill of Material by eliminating colds leads, support brackets and insulation entry kits

Connections are made directly into Cage clamp terminals which are simple to use and very reliable

Hazardous areas approved

Design validation for specific applications, fully supported by nVent design software TraceCalc Pro

ESPECIFICACIONES

Table 1/2

Número de catálogo	Tipo de conexión	Material	Montaje	Clasificación IP	Ambient Temperature	Cable Entry
P000004432	Cold Applied	Glass Fiber Reinforced Polymer	On Pipe	IP66	-55 to 56 °C	N.A.

Table 2/2

Número de catálogo	Knockouts Included	Cover Attachment	Max Conductor Cross Section	Libre de halógenos	Connection Clamp Quantity	Area Classification
P000004432	No	Screwed	16 mm ²	Sí	5	Non-Hazardous, Hazardous

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT