


19" Pusher Fan, 3 U, Axial

Servicios públicos de energía

Fan tray with integrated pusher fan.



CERTIFICACIONES



CARACTERÍSTICAS

Ventilation directed accurately to the electronics

19" Pusher Fan, 3 U, Axial

Air infeed from front, air exits at the top rear of cabinet (guided upwards by cover plates or via hoses to rear and upwards)

Contact protection in accordance with DIN EN ISO 13857

ESPECIFICACIONES

Table 1/1

Número de catálogo	Input Voltage AC
10713-546	230 V min
10713-547	115 V min

ADDITIONAL PRODUCT DETAILS

With cover plates, this pusher fan can be re-fitted to different cooling concepts

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE