



Single phase monitored PDU

Input Rating : 20A, 110V
 Outlet : 20A Rated US NEMA 5-20R x 24
 Inlet : 20A NEMA L5-20P plug
 Cordset : 3 meter UL 12AWG cordset
 Protection : Nil
 Circuit Details : Output 16A max. U.S # 1 - 2 4

Meter Features (W monitored PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
 Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
 Accuracy : ±1% Billing-grade
 IP Access : via IP dongle, one IP Access up to 16 PDU Levels
 Cascade : Up to 16 PDU under single IP address via IP dongle
 SNMP : V2 / V3 via IP dongle
 Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

Chassis Material : Steel
 Chassis Color : Black
 Product Dimension : 2.1 (W) x 3.1 (D) x 53.15 (H) mm
 Net Weight : 23.5 lbs
 Packing dimension (for 2 PDUs) : 4.3 (W) x 10.6 (D) x 70.6 (H) inch
 PDU gross weight (for 2 PDUs) : 55.4 lbs

EMC Compliance : FCC Part 15 Subpart B certified
 Safety Compliance : cTUVus Mark to UL 60950-1:2007/R:2014-10
 CAN/CSA-C22.2 No. 60950-1:2007/A2:2014-10
 UL 62368-1:2014
 CAN/CSA-C22.2 No. 62368-1:2014
 UL 60730-1 Ed.5 (2016)
 Environment Compliance : RoHS2 & REACH
 Operating Temperature : -5 to 60 °C
 Storage Temperature : -25 to 65 °C
 Operating Altitude : 0 to 2,000 m
 Storage Altitude : 0 to 15,000 m
 Humidity : 8 to 95% RH, non-condensing