

# MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base

## Servicios públicos de energía



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

### CERTIFICACIONES



### CARACTERÍSTICAS

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Rack Height | Profundidad | Usable Width | Montaje | Cumple con                       | EMC Shielding      |
|--------------------|-------------|-------------|--------------|---------|----------------------------------|--------------------|
| 20860-621          | 1 U         | 220 mm      | 403 mm       | Rack    | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-622          | 1 U         | 280 mm      | 403 mm       | Rack    | IEC 60297-3-100, IEC 60297-3-105 | No (Retrofittable) |
| 20860-625          | 2 U         | 280 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-626          | 2 U         | 340 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-627          | 3 U         | 280 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-628          | 3 U         | 340 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-629          | 3 U         | 400 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-632          | 4 U         | 340 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-633          | 4 U         | 400 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-634          | 4 U         | 460 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |
| 20860-635          | 5 U         | 460 mm      | 403 mm       | Rack    | IEC 60297-3-100                  | No (Retrofittable) |

Table 2/2

| Número de catálogo | Product Family | Product Type    | Tipo      |
|--------------------|----------------|-----------------|-----------|
| 20860-621          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-622          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-625          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-626          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-627          | MultipacPRO    | Subrack/Chassis | Perforado |

| Número de catálogo | Product Family | Product Type    | Tipo      |
|--------------------|----------------|-----------------|-----------|
| 20860-628          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-629          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-632          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-633          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-634          | MultipacPRO    | Subrack/Chassis | Perforado |
| 20860-635          | MultipacPRO    | Subrack/Chassis | Perforado |

### ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

### ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**