

On Demand Stock Panels: NGC-40



nVent RAYCHEM NGC-40 On Demand Stock Panels offer rapid delivery of optimized best-in-class standard panel configurations for customer projects. Panels are built with quality components including premium RAYCHEM controllers for use in hazardous and nonhazardous areas. Many configurations have C1D2 circuit breakers and Type 4X stainless steel enclosures.

CARACTERÍSTICAS

Improve efficiency and reduce lead times by using standardized EHT controller & panel designs

Broad selection of configurations available immediately with best-in-class advanced control options

Consistent design with time-tested quality for your project

ESPECIFICACIONES

Table 1/1

Número de catálogo	Circuit Breaker Voltage Rating	Main Circuit Breaker Current Rating	Pantalla táctil incluida	Control Relay Type	Voltage Rating
101723-001			No	Solid State	277 – 480 V
101723-003	277 V	70 A	No	Solid State	277 – 480 V
101723-002	277 V	50 A	No	Solid State	277 – 480 V
101723-005	277 V	175 A	No	Solid State	277 – 480 V
101723-004	277 V	125 A	No	Solid State	277 – 480 V

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de

atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT