

HN 3R Side-Mount Filter Fans Reverse 115V, 5.91 x 5.91 x 2.92, Negro, Plástico

NÚMERO DE CATÁLOGO

HN0516513R



HN 3R Side-Mount Filter Fans quickly install into enclosure with a click-fit design; no tools or screws required. Grilles open with the flick of a finger for easy filter replacement.

ESTÁNDARES DEL SECTOR

UL/cUL Listed; File No. E482010

CE, UK CA, UL

Type 12, 3R standard

IP55 standard on all models except HN04

CARACTERÍSTICAS

Click-fit design quickly installs into enclosure wall; no tools or screws required

Grille opens with the flick of a finger for easy filter replacement

Enclosure side wall mounting

Reverse airflow option on items ending with "R" available to push/pull air through higher static pressure

Standard rope gasket provides proper seal to the enclosure

Similar cut-out sizes as other filter fan manufacturers

Terminal block connections

Optional thermostat available to save energy and extend service life

Hinged grille remains attached after opening

Size range from 4 in. (102 mm) to 12 in. (305 mm)

Service life hours from 40,000 to 98,000 hours

ATRIBUTOS DEL PRODUCTO

Número de artículo: 59934

Flujo de aire: 56m³/h

Tensión nominal: 115V

Altura: 150mm

Anchura: 150mm

Fondo: 74mm

Corriente máxima: 0.26A

Temperatura de funcionamiento: -10 to 55°C

Material: De plástico

Acabado: Suave mate

Color: Negro

Código de color: RAL 9005

DETALLES ADICIONALES DEL PRODUCTO

Unit depth is of the entire unit.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE