

Modular Single Door, MCSS-HP

Power Utilities



The stainless steel single door modular floor standing enclosure range, MCSS-HP, with a IP 66 protection degree offers a higher protection level for equipment and components which will help extend their lifetime and reduce maintenance costs when the enclosure is installed for rough environments with severe conditions. These new enclosures are rated as IP66 even if they are bayed between them using the standard baying brackets.

ESTÁNDARES DEL SECTOR

NEMA Type 4X, 12, 13

IP66

IK10

CARACTERÍSTICAS

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660 including integrated external hole pattern

Door: Mounted with four hinges, allowing left or right hand opening; ncluding door frame with 25 mm hole pattern

Rear panel: Fitted by M6 torx screws; standard facilities for rear door mounting

Supplied as an accessory

Removable roof panel

Lock: Espagnolette 4-point locking system which does not interfere with the enclosure inner space; standard double-bit lock with 3 mm insert

Bottom plate: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing

Mounting plate: Double folded and slides into position with adjustable depths of 25 mm, with the MPD02 accessory

Earthing/Grounding: All panels are earthed/grounded through their fittings and equipped with a separate earthing stud

Mounting requirements: For stand-alone installation, add side panels; for combined installation, HPPG01 and baying brackets, CCI and CCM are required

Delivery: Frame with fitted door, rear panel, roof panel, bottom plate, mounting plate and door frame; delivery also includes earthing bolts

ESPECIFICACIONES

Table 1/2

Número de catálogo	Número de artículo	Altura	Anchura	Fondo	Material	Acabado
MCSS20086HP	MCSS20086HP	2000 mm	800 mm	600 mm	Acero inoxidable	Cepillado

Table 2/2

Número de catálogo	Número de artículo	Color	Grosor del cuerpo	Grosor de puerta
MCSS20086HP	MCSS20086HP	Sin pintar	1.5 mm	2 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE