

Modular Single Door, MCSS

Servicios públicos de energía



The stainless steel single door modular floor standing enclosure range, MCSS, with a IP 55 protection degree, is available off the shelf in many different sizes. The risk for component failure, and with that unnecessary downtime, is eliminated as water and dust are prevented from entering the enclosure. This enclosure range is well suited for almost any environment, grade dependent.

INDUSTRY STANDARDS

UL 508A Listed; Type 12; File No. E92044
 cUL Listed per CSA C22.2 No.0, No.0.4, No.14, No.94; Type 12; File No. E92044
 NEMA/EEMAC Type 12
 CSA, File No. 1442951: Type 12
 IEC 62208 IP55
 KEMA, GOST, Lloyds, CE, EAC

CARACTERÍSTICAS

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660

Door: Mounted with four hinges allowing left or right hand opening; including door frame with 25 mm hole pattern

Rear panel: Fitted by M6 torx screws; standard facilities for rear door mounting

Supplied as an accessory

Removable roof panel

Lock: Espagnolette 4-point locking system which does not interfere with the enclosure inner space; standard double-bit 3 mm insert

Bottom plate: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing

Mounting plate: Double folded and slides into position with adjustable depths of 25 mm, with the MPD02 accessory

Earthing/Grounding: All panels are earthed/grounded through their fittings and equipped with a separate earthing stud

Mounting requirements: Standard delivery ready for combined installation; for stand-alone installation, add side panels

Delivery: Frame with fitted door, rear panel, roof panel, bottom plate, mounting plate and door frame; delivery also includes earthing bolts

ESPECIFICACIONES

- Body Thickness:

1,5 mm
- Door Thickness:

2 mm
- Acabado:

Brushed
- Material:

Acero inoxidable
- Color:

Unpainted

Table 1/1				
Número de catálogo	Número de artículo	Altura	Ancho	Profundidad
MCSS18085	MCSS18085	1800 mm	800 mm	500 mm
MCSS18065	MCSS18065	1800 mm	600 mm	500 mm
MCSS20086	MCSS20086	2000 mm	800 mm	600 mm
MCSS20066	MCSS20066	2000 mm	600 mm	600 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDYERICOHOFFMANILSCOSCHROFFTRACHTE