

RackPower Basic PDU, RB0xxx, 208 VAC, 3-phase

Servicios públicos de energía

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

CARACTERÍSTICAS

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200-240VAC, 3-phase DELTA

Connecting cable 6", with IEC 60309 3P+E connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

ESPECIFICACIONES

Table 1/2

Número de catálogo	Product Type	Socket Type	Color	Longitud	Voltage AC	Profundidad
RB0952	Socket Strip	IEC C13, IEC C13/C19	Negro	1780 mm	208 V	75 mm

Table 2/2

Número de catálogo	Ancho
RB0952	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE