

NGC-40 Series, Bridge Module



nVent RAYCHEM NGC-40 Series - Bridge Module provides the interface between a panel's internal CAN-based network and upstream devices. Multiple communication ports are supported, allowing serial and ethernet connections to be used with external devices: Each has two RS-485 ports, one RS-232 port and one 10/100 Base-T ethernet network with programmable communication parameters. A maximum of 80 NGC-40 modules, a combination of HTC, HTC3 or input/output modules, can be connected to one NGC-40-BRIDGE module.

CARACTERÍSTICAS

Provides the interface between the NGC-40 system and any upstream devices

Also used to communicate with other HTC modules in the NGC-40 system

ESPECIFICACIONES

Table 1/2

Número de catálogo	Nombre del artículo	Tensión nominal	Tipo de tensión nominal	Temperatura de funcionamiento	Compatible con protocolo CAN	Cantidad de módulos
10730-002	NGC-40-BRIDGE	24 V	DC	-40 to 65 °C	Sí	80

Table 2/2

Número de catálogo	Nombre del artículo	Altura	Anchura	Fondo
10730-002	NGC-40-BRIDGE	87 mm	45 mm	106.4 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Nuestra poderosa cartera de marcas:

RAYCHEM PYROTENAX TRACER NUHEAT