

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Servicios públicos de energía

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICACIONES



CARACTERÍSTICAS

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-191	3 U	175 mm	1	DIN Connector	160 mm	Acero inoxidable
24563-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acero inoxidable
24563-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acero inoxidable
24563-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable
24563-491	6 U	175 mm	1	DIN Connector	160 mm	Acero inoxidable
24563-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Acero inoxidable
24563-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Acero inoxidable
24563-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Acero inoxidable

Table 2/3

Número de catálogo	Handle Included	Montaje	Cumple con	EMC Shielding	Product Type	Rack Width
24563-191	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-192	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-193	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-194	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-491	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-492	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24563-493	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Número de catálogo	HandleIncluded	Montaje	Cumple con	EMC Shielding	Product Type	Rack Width
24563-494	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Número de catálogo	Carga estática
24563-191	11 kgf
24563-192	11 kgf
24563-193	11 kgf
24563-194	11 kgf
24563-491	11 kgf
24563-492	11 kgf
24563-493	11 kgf
24563-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE