

RackPower Basic PDU, RB0xxx, 100-240 VAC, 1-phase

Servicios públicos de energía

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

CARACTERÍSTICAS

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

ESPECIFICACIONES

Table 1/2

Número de catálogo	Product Type	Socket Type	Color	Longitud	Voltage AC	Profundidad
RB0322	Socket Strip	IEC C13, IEC C19	Negro	817 mm	230 V	53 mm

Table 2/2

Número de catálogo	Ancho
RB0322	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE