

RackPower PDU, RP2xxx, 100-240 VAC, 1-phase

Servicios públicos de energía

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

CARACTERÍSTICAS

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 240 VAC, 1-phase L-N or L-L

Input connector C20

C13, C19 outlets

User-defined power-on time delay or automatic power-on sequencing

ESPECIFICACIONES

Table 1/2

Número de catálogo	Product Type	Socket Type	Color	Longitud	Voltage AC	Function
RP2326	Socket Strip	IEC C13, IEC C19	Negro	1490 mm	230 V	Input Monitored, Switched Outlets

Table 2/2

Número de catálogo	Profundidad	Ancho
--------------------	-------------	-------

RP2326	53 mm	52 mm
--------	-------	-------

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE