

Novastar Cabinet With Glazed Door and Rear Panel

Servicios públicos de energía



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFICACIONES



CARACTERÍSTICAS

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Frame Color	Altura	Frame Color Code	Cladding Material	Ancho
--------------------	-------------	-------------	--------	------------------	-------------------	-------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Acero	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Acero	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Acero	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Acero	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Acero	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Acero	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Acero	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Acero	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Acero	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Acero	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Acero	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Acero	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Acero	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Acero	553 mm

Table 2/3						
Número de catálogo	Cladding Color	Profundidad	Carga estática	Cladding Color Code	Cumple con	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio

Número de catálogo	Cladding Color	Profundidad	Carga estática	Cladding Color Code	Cumple con	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminio
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminio

Table 3/3

Número de catálogo	Product Type	Protection Rating
15230-019	Gabinete	IP20
16230-019	Gabinete	IP20
15230-020	Gabinete	IP20
16230-020	Gabinete	IP20
15230-021	Gabinete	IP20
16230-021	Gabinete	IP20

Número de catálogo	Product Type	Protection Rating
15230-022	Gabinete	IP20
15230-023	Gabinete	IP20
16230-022	Gabinete	IP20
16230-023	Gabinete	IP20
15230-024	Gabinete	IP20
15230-025	Gabinete	IP20
16230-024	Gabinete	IP20
16230-025	Gabinete	IP20

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE