

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

Servicios públicos de energía

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

CARACTERÍSTICAS

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Altura	Frame Color	Ancho	Frame Color Code	Cladding Material
10630-033	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acero
10630-034	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Acero
10630-035	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acero
10630-036	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Acero

Table 2/3

Número de catálogo	Profundidad	Cladding Color	Cladding Color Code	Cumple con	Frame Material	Product Type
--------------------	-------------	----------------	---------------------	------------	----------------	--------------

10630-033	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Acero	Gabinete
10630-034	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Acero	Gabinete
10630-035	600 mm	Black Grey	RAL 7021	IEC 60297-3-100	Acero	Gabinete
10630-036	800 mm	Black Grey	RAL 7021	IEC 60297-3-100	Acero	Gabinete

Table 3/3

Número de catálogo	Carga estática
10630-033	400 kgf
10630-034	400 kgf
10630-035	400 kgf
10630-036	400 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE