

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Servicios públicos de energía

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

CARACTERÍSTICAS

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

ESPECIFICACIONES

Table 1/3

Número de catálogo	Rack Height	Altura	Ancho	Color	Color Code	Cumple con
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Número de catálogo	Acabado	Locking Type	Material	Product Type	Protection Rating	Tipo
21630-823	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated
21630-820	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Recubrimiento de polvo	3-Point Locking, Electronic	Acero	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Número de catálogo	Works With
21630-823	Varistar CP
21630-822	Varistar CP
21630-820	Varistar CP
21630-825	Varistar CP
21630-824	Varistar CP
21630-821	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE