

Varistar CP EMC Cabinet, IP 55

Power Utilities



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

CARACTERÍSTICAS

Shielding 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3)

Shielding 30 dB at 18 GHz, (tested to EN 61000-5-7) with EN45545 gaskets

Type of protection IP 55

Static load-carrying capacity 1600 kg

Doors with 4-point locking and screw-fixed side panels

Side and rear panels can be installed by one person

ESPECIFICACIONES

Table 1/3

Número de catálogo	Altura del rack	Altura	Color del bastidor	Anchura	Código de color del bastidor	Material de revestimiento
10630-044	42 U	2000 mm	Gris negro	600 mm	RAL 7021	Acero
10630-043	42 U	2000 mm	Gris negro	600 mm	RAL 7021	Acero

Table 2/3

Número de catálogo	Fondo	Color de revestimiento	Código de color de revestimiento	De conformidad con	Material del bastidor	Tipo de producto
--------------------	-------	------------------------	----------------------------------	--------------------	-----------------------	------------------

10630-044	800 mm	Gris negro	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Acero	Gabinete
10630-043	800 mm	Gris negro	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-3	Acero	Gabinete

Table 3/3		
Número de catálogo	Grado de protección	Carga estática
10630-044	IP55	1600 kgf
10630-043	IP55	1600 kgf

DETALLES ADICIONALES DEL PRODUCTO

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE