

# Varistar CP IP 55 Cabinet

## Servicios públicos de energía

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP20 and IP55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

### CARACTERÍSTICAS

Type of protection IP 55

Doors with 3-point locking and screw-fixed side panels

Static load-carrying capacity 1600 kg

Side and rear panels can be installed by one person

EN45545-2 fire safety Gaskets

### ESPECIFICACIONES

Table 1/3

| Número de catálogo | Rack Height | Altura  | Frame Color | Ancho  | Frame Color Code | Cladding Material |
|--------------------|-------------|---------|-------------|--------|------------------|-------------------|
| 10630-041          | 42 U        | 2000 mm | Black Grey  | 600 mm | RAL 7021         | Acero             |
| 10630-042          | 42 U        | 2000 mm | Black Grey  | 600 mm | RAL 7021         | Acero             |

Table 2/3

| Número de catálogo | Profundidad | Cladding Color | Cladding Color Code | Cumple con                              | Frame Material | Product Type |
|--------------------|-------------|----------------|---------------------|-----------------------------------------|----------------|--------------|
| 10630-041          | 600 mm      | Black Grey     | RAL 7021            | IEC 60529, IEC 61587-1, IEC 60297-3-100 | Acero          | Gabinete     |

| Número de catálogo | Profundidad | Cladding Color | Cladding Color Code | Cumple con                              | Frame Material | Product Type |
|--------------------|-------------|----------------|---------------------|-----------------------------------------|----------------|--------------|
| 10630-042          | 600 mm      | Black Grey     | RAL 7021            | IEC 60529, IEC 61587-1, IEC 60297-3-100 | Acero          | Gabinete     |

Table 3/3

| Número de catálogo | Protection Rating | Carga estática |
|--------------------|-------------------|----------------|
| 10630-041          | IP55              | 1600 kgf       |
| 10630-042          | IP55              | 1600 kgf       |

## ADDITIONAL PRODUCT DETAILS

Further dimensions and versions available on ServicePLUS IP 55. Please order base/plinth separately. For the assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**