

MONI-PT100-4/20MA Sensor Assembly for Hazardous Areas



nVent RAYCHEM MONI-PT100-4/20MA is a PT100 sensor connected to a 4-20 mA transmitter built into a black glass fiber reinforced polyester junction box. Suitable for hazardous areas.

CARACTERÍSTICAS

Simple and fast to install: built in a black glass fiber reinforced polyester junction box with blue M20 cable gland

Temperature measuring range: -50 °C to +250 °C

ESPECIFICACIONES

Table 1/2

Número de catálogo	Nombre del artículo	Housing Material	Montaje	Max Measuring Range	Temperatura de funcionamiento	Fixed Cable to Sensor
704058-000	PT100-4/20MA	Poliéster reforzado con fibra de vidrio	Bracket	250 °C	-20 to 55 °C	Sí

Table 2/2

Número de catálogo	Nombre del artículo	Longitud del cable	Sensor Tip Diameter
704058-000	PT100-4/20MA	2 m	3 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT