

T2Green-5 Underfloor Heating Loose Cable



nVent RAYCHEM T2Green-5 is a constant power output floor heating cable delivering 5 W/m. Ideal for low energy buildings and passive houses, to provide additional comfort. It is dual conductor with a pre-terminated 2.5 m cold lead, available in lengths from 15 m to 115 m.

CARACTERÍSTICAS

Simple and fast to install

Easy design: one cold lead connection due to dual wire cable design, different power outputs/m² obtained by varying the spacing

Low energy consumption and eco-design compatible: low power output heating cable, lower energy consumption when used with a nVent RAYCHEM smart thermostat

Reliable during long life: 12 year product warranty available

ESPECIFICACIONES

Cold Lead Length:	2,5 m
Nominal Power Output:	5 W/m
Diámetro exterior:	5,5 mm
Power Output, Typical:	30 – 50 W/m ²
Min Cable Spacing:	50 mm
Max Continuous Exposure Temperature, Power Off:	90 °C
Tensión nominal:	230 V
Ground Path Type:	Trenzado
Heating Cable Technology:	Constant Wattage
Color:	Verde
Outer Jacket Material:	Low Smoke Zero Halogen

Table 1/1

Número de catálogo	Nombre del artículo	Energía	Resistance Range	Longitud
SZ18300122	R-GR-15M/T0/SD	65 W	755.3 – 874.5 Ω	15 m

Número de catálogo	Nombre del artículo	Energía	Resistance Range	Longitud
SZ18300123	R-GR-20M/T0/SD	110 W	448.4 – 519.2 Ω	20 m
SZ18300124	R-GR-25M/T0/SD	160 W	315.9 – 365.8 Ω	25 m
SZ18300125	R-GR-35M/T0/SD	180 W	282.6 – 327.3 Ω	35 m
SZ18300126	R-GR-40M/T0/SD	230 W	220.4 – 255.2 Ω	40 m
SZ18300127	R-GR-50M/T0/SD	245 W	204.3 – 236.5 Ω	50 m
SZ18300128	R-GR-60M/T0/SD	340 W	148.2 – 171.6 Ω	60 m
SZ18300129	R-GR-70M/T0/SD	360 W	139.7 – 161.7 Ω	70 m
SZ18300130	R-GR-85M/T0/SD	425 W	117.9 – 136.5 Ω	85 m
SZ18300131	R-GR-100M/T0/SD	490 W	102.6 – 118.8 Ω	100 m
SZ18300132	R-GR-115M/T0/SD	560 W	89.6 – 103.7 Ω	115 m

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT