

T2Red and Reflecta Self-Regulating Floor Heating System



nVent RAYCHEM T2Red and Reflecta combines a self-regulating floor heating cable with perfect heat spreading and insulation boards. Suitable for new build and renovation, they can be applied under any type of floor surface without risk of overheating. Ideal for wooden and engineered wooden floors but also for natural stone and ceramic tiles.

CARACTERÍSTICAS

Energy efficient and self regulating: automatically adjusts heat output, more heat near windows, less heat under furnishings

Maximum comfort with T2Reflecta insulation board: heat spreads perfectly over the entire room

Simple, fast installation: cut-to-length, no cold leads, If combined with Reflecta then pre-grooves serve as cable fixing tool and guarantee perfect cable distance of 100-200 or 300mm spacing, suitable for all sub-floors and floor coverings, meter markings, user-friendly connections kits

Safe and efficient operation: fast heat up, uniform temperatures across the room, flexible power output from 35-100W/m², closer loops for higher output and wider loops for lower output, no overheating

Reliable during long life: 12 to 20 year total care warranty available, no maintenance required

Advanced control options available

ESPECIFICACIONES

Table 1/3

Número de catálogo	Nombre del artículo	Heating Cable Technology	Tensión nominal	Power Output	Power Output, Typical	Outer Jacket Material
948739-000	T2-RED	Self-Regulating	230 V	5 – 15 W/m	80 – 125 W/m ²	Fluoropolímero

Table 2/3

Número de catálogo	Nombre del artículo	Color	Ground Path Type	Temperatura de instalación mín.	Nominal Width	Nominal Height

948739-000	T2-RED	Rojo	Trenzado	5 °C	8.5 mm	5.8 mm
------------	--------	------	----------	------	--------	--------

Table 3/3

Número de catálogo	Nombre del artículo	Nominal Cable Weight	Max Circuit Length	Circuit Breaker
948739-000	T2-RED	68 g/m	100 m	Type C/10Amp

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

Norteamérica

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latinoamérica

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT