

EuropacPRO 19" Subrack Kit for Backplane, Shielded

Servicios públicos de energía

EMC Shielded subrack for backplane mounting, rear side covered by a rear panel.



CERTIFICACIONES



CARACTERÍSTICAS

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

IP 20, in accordance with IEC 60529

Aluminum construction

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "light"

ESPECIFICACIONES

Product Type: Subrack/Chassis

Table 1/2						
Número de catálogo	Rack Height	Profundidad	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-142	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-143	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-144	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-145	3 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-146	3 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-442	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-443	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-444	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-445	6 U	415 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-446	6 U	475 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/2						
Número de catálogo	Handle Included	Montaje	Cumple con	EMC Shielding	Rack Width	Carga estática
24563-142	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-143	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-144	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-145	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf

Número de catálogo	HandleIncluded	Montaje	Cumple con	EMC Shielding	Rack Width	Carga estática
24563-146	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-442	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-443	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-444	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-445	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf
24563-446	No	Rack	IEC 60297-3-103	Sí	84 HP	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE