


MultipacPRO 19" Chassis Basic Kit

Servicios públicos de energía

Such a kit enables a customer to configure the 3 different top / bottom covers.



CERTIFICACIONES



CARACTERÍSTICAS

For non-standardized assemblies (1 ... 5 U) and standardized assemblies (1, 2 U) conforming to IEC 60297-3-105

Frame consists of two lateral parts and front/rear panel

Material: aluminium

Select further components (Accessories)

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Height	Profundidad	Usable Width	Montaje	Cumple con	EMC Shielding
20860-201	1 U	220 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-202	1 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Número de catálogo	Rack Height	Profundidad	Usable Width	Montaje	Cumple con	EMC Shielding
20860-203	1 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-210	2 U	220 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-211	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-212	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-219	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-220	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-221	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-222	3 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-228	4 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-229	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-230	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-231	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-240	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Número de catálogo	Product Family	Product Type	Tipo
20860-201	MultipacPRO	Subrack/Chassis	Configurable
20860-202	MultipacPRO	Subrack/Chassis	Configurable
20860-203	MultipacPRO	Subrack/Chassis	Configurable
20860-210	MultipacPRO	Subrack/Chassis	Configurable

Número de catálogo	Product Family	Product Type	Tipo
20860-211	MultipacPRO	Subrack/Chassis	Configurable
20860-212	MultipacPRO	Subrack/Chassis	Configurable
20860-219	MultipacPRO	Subrack/Chassis	Configurable
20860-220	MultipacPRO	Subrack/Chassis	Configurable
20860-221	MultipacPRO	Subrack/Chassis	Configurable
20860-222	MultipacPRO	Subrack/Chassis	Configurable
20860-228	MultipacPRO	Subrack/Chassis	Configurable
20860-229	MultipacPRO	Subrack/Chassis	Configurable
20860-230	MultipacPRO	Subrack/Chassis	Configurable
20860-231	MultipacPRO	Subrack/Chassis	Configurable
20860-240	MultipacPRO	Subrack/Chassis	Configurable

ADDITIONAL PRODUCT DETAILS

Please order mounting plate, cover and base plates, handles, telescopic slides separately.

Dimensions h = clear mounting height = H-8.1 mm, b = clear mounting width = 403 mm.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE