

RackPower PDU, RP1xxx, 120 VAC, 1-phase

Servicios públicos de energía

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

CARACTERÍSTICAS

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100 - 120 VAC, 1-phase L-N

Connecting cable 10", with NEMA L5 connector

Nema L5 outlets

ESPECIFICACIONES

Table 1/2

Número de catálogo	Product Type	Socket Type	Color	Longitud	Voltage AC	Function
RP1316	Socket Strip	NEMA 5-20R	Negro	817 mm	120 V	Input Monitored
RP1327	Socket Strip	NEMA 5-20R	Negro	1490 mm	120 V	Input Monitored

Table 2/2

Número de catálogo	Profundidad	Ancho
RP1316	53 mm	52 mm

Número de catálogo	Profundidad	Ancho
RP1327	53 mm	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE