

# RackPower PDU, RP2xxx, 230/400 VAC, 3-phase

## Servicios públicos de energía

Modular, compact intelligent PDU with inlet metering and remote outlet switching. Ultra-Low Profile Design with only 50 mm height.

### CARACTERÍSTICAS

RackPower RP2xxx Intelligent Power Distribution Units monitors input power of the entire PDU and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

User-defined power-on time delay or automatic power-on sequencing

### ESPECIFICACIONES

Table 1/2

| Número de catálogo | Product Type | Socket Type          | Color | Longitud | Voltage AC | Function                          |
|--------------------|--------------|----------------------|-------|----------|------------|-----------------------------------|
| RP2950             | Socket Strip | IEC C13, IEC C13/C19 | Negro | 1826 mm  | 230 V      | Input Monitored, Switched Outlets |
| RP2850             | Socket Strip | IEC C13, IEC C13/C19 | Negro | 1780 mm  | 230 V      | Input Monitored, Switched Outlets |

| Número de catálogo | Product Type | Socket Type          | Color | Longitud | Voltage AC | Function                          |
|--------------------|--------------|----------------------|-------|----------|------------|-----------------------------------|
| RP2450             | Socket Strip | IEC C13, IEC C13/C19 | Negro | 1490 mm  | 230 V      | Input Monitored, Switched Outlets |

| Table 2/2          |             |       |
|--------------------|-------------|-------|
| Número de catálogo | Profundidad | Ancho |
| RP2950             | 75 mm       | 56 mm |
| RP2850             | 75 mm       | 56 mm |
| RP2450             | 75 mm       | 56 mm |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en [www.nvent.com](http://www.nvent.com) y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE