

Varistar CP Steel Door, Plain With 3-Point Locking, IP20

Servicios públicos de energía

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

CARACTERÍSTICAS

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Height	Altura	Ancho	Color	Color Code	Cumple con
21630-104	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-105	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-106	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-107	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-108	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-109	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-432	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Número de catálogo	Rack Height	Altura	Ancho	Color	Color Code	Cumple con
21630-433	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-434	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-435	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-436	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-437	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-438	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-439	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Número de catálogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-104	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-105	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-106	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-107	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-108	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-109	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-432	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-433	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-434	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP

Número de catálogo	Locking Type	Product Type	Protection Rating	Tipo	Works With
21630-435	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-436	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-437	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-438	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-439	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE