

NGC-40 Series, Power Termination Module



nVent RAYCHEM NGC-40 Series - Power Termination Module accepts a primary and redundant power supply input, also accepts CAN bus inputs and provides for termination of the CAN bus. Each NGC-40-PTM can provide power for a maximum of 10 NGC-40 modules.

CARACTERÍSTICAS

Din-rail mounted and part of the NGC-40 system

Provides primary power and CAN bus inputs/termination to the NGC-40 system

Easy to install and reliable

ESPECIFICACIONES

Table 1/2

Número de catálogo	Nombre del artículo	Tensión nominal	Tipo de tensión nominal	Corriente nominal a 24 V CC	Temperatura de funcionamiento	Altura
10730-005	NGC-40-PTM	24 V	DC	1.5 A	-40 to 65 °C	87 mm

Table 2/2

Número de catálogo	Nombre del artículo	Anchura	Fondo
10730-005	NGC-40-PTM	45 mm	106.4 mm

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Nuestra poderosa cartera de marcas:

RAYCHEM PYROTENAX TRACER NUHEAT