

Horizontal Rail, Front, Type R-KD, Rugged, Short Lip, 84 HP

Power Utilities

NÚMERO DE CATÁLOGO

34566-284



Combinations of horizontal rails and side panels

 = can be combined.
  = combination not recommended

	Light rail	Frontier F	Heavy rail	Rugged rail
Light rail	-	network F allowed for connection to the network	network F for heavy rail connection to the network	network F supported
Frontier F	+	+	+	+
Heavy rail	+	network F not allowed	network F for heavy rail	-
Rugged rail	+	+	-	-

side panel
 




1000 x 1000 mm
 1000 x 1500 mm
 1500 x 1000 mm
 1500 x 1500 mm

[Go to Support center](#)

The rugged horizontal rail type can handle shock and vibration up to 25 g.

CERTIFICACIONES



CARACTERÍSTICAS

Type R-KD "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

ATRIBUTOS DEL PRODUCTO

Tipo de producto: Carril horizontal

Familia de productos: EuropacPRO

Tipo: Robusto, KD

Ancho del rack: 84 HP

Longitud: 431.8 mm

DETALLES ADICIONALES DEL PRODUCTO

Without M4 thread to front, without printing and without notch for 19" bracket.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Nuestro gran portafolio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE