

EuropacPRO Rugged Rear Angle for Textile EMC Gasket

Servicios públicos de energía



Corner profile covers the slot between the side panel and the rear panel of a subrack. Needed for a proper EMC shielding.

CERTIFICACIONES



CARACTERÍSTICAS

Required for shielding of rear

Can also be used as front closure when using a depth-adjustable 19" support bracket

ESPECIFICACIONES

Table 1/2

Número de catálogo	Rack Height	Package Quantity	Altura	Product Family	Product Type	Tipo
24566-499	6 U	1	265.9 mm	EuropacPRO	Cubierta	Rugged
24566-197	3 U	1	132.6 mm	EuropacPRO	Cubierta	Rugged

Número de catálogo	Rack Height	Package Quantity	Altura	Product Family	Product Type	Tipo
24566-199	3 U	1	132.6 mm	EuropacPRO	Cubierta	Rugged
24566-497	6 U	1	265.9 mm	EuropacPRO	Cubierta	Rugged

Table 2/2			
Número de catálogo	Works With	Unidades en el empaque	Certificaciones
24566-499	Subracks	Par	RoHS
24566-197	Subracks	Par	
24566-199	Subracks	Par	RoHS
24566-497	Subracks	Par	

ADDITIONAL PRODUCT DETAILS

Please order EMC textile gasket separately.

Corner profile cannot be used together with adapter for rear mounting.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE